Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub





M12A-04PMMR-SF8001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Metal, Non-shielded
- Jacket Material: N/A
- Certificate: UL1977, UL2238, UL1863

You must login first for view the price


Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type ▾ Search



M Series,...	M Series,...	M Series,...	M Series,...	M Series, M12, A...	M Series, M12, A...
CAP-WBDMQPC1 -20°C ~ +80°C	CAP-WBDMSMA2 -40°C ~ +105°C	CAP-WBDMSPB2 -40°C ~ +105°C	IA-A04F-A04F-... -20°C ~ +85°C	M12A-04BFFA-... -40°C ~ +105°C	M12A-04BFFB-... -40°C ~ +105°C
− 0 +	− 0 +	− 0 +	− 0 +	− 0 +	− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **4A**	Connector Type **Receptacle**
Shielded **Metal, Non-shielded**	No. of Contacts **04**
Connector Gender **Male**	Backshell **Hexagonal**
Mating Style **Screw Thread**	IP Rating **IP68**
Assembly Style **PCB 90°**	

More Options

People Also Bought



M12A-04PMMR-...	BD-04PMMM-LL7A05	SSL11-J4L2J-T22D06	AB-BD04ML-BDHL-...	1CB-05AMFM-LL7A03

Downloaded from Arrow.com.