
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECN-22-148334	08APR2022	W.H	L.C
	A1	REVISED PER ECR-22-136510	25MAY2022	N.H	L.C



1. MATERIAL:
HOUSING:PBT,UL94-V0 COLOR: NATURAL
PIN CONTACT: COPPER ALLOY, 2.0µm MIN TIN OVER 1.25µm MIN NICKEL OVERALL.

2. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.


3. CONTACT SOLDERTAIL KINK DIRECTION(BOARDLOCK) SEE PAGE 2.


4. RECOMMENDED MATING PART:1744417-[ ]


5. PACKAGING: LOOSE PIECE.


6. PER IEC 60335-1 SECT. 30, GWEPT 750C, NO FLAME or Te-Ti≤2S.


7. HIGH TEMPERATURE VERSION, MEET HEAT RESISTANCE FOR SOLDERING TEMPERATURE 260~265°C, DURATION 5 +2/-0 Sec.












THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W. HUO 06DEC2021	TE Connectivity
		CHK L. CHEN 07DEC2021	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. ZHANG 08DEC2021	NAME HEADER ASSEMBLY, VERTICAL GLOW WIRE, WITH BOSS, EP2.5 -
	0 PLC ±- 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±3°	PRODUCT SPEC 108-2418	
		APPLICATION SPEC 114-13315	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-2404280 / RESTRICTED TO -
MATERIAL 1	FINISH - -	WEIGHT -	CUSTOMER DRAWING / SCALE 5:1 / SHEET 1 OF 2 / REV A1


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2 POSITION




3 POSITION




4 POSITION




5 POSITION




6 POSITION




7 POSITION



8 POSITION



9 POSITION



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05

△3

●: KINKED PIN ○: NO KINK										
							●	●	●	2P
						●	○	●	3P	
					●	○	○	●	4P	
				●	○	○	○	●	5P	
			●	○	○	○	○	●	6P	
		●	○	○	●	○	○	●	7P	
	●	○	○	○	●	○	○	●	8P	
●	○	○	○	●	○	○	○	●	9P	
9	8	7	6	5	4	3	2	1	POS	

DIM C	DIM B	DIM A	POS	PART NO
20.0	23.33	25.0	9	2404280-9
17.5	20.83	22.5	8	2404280-8
15.0	18.33	20.0	7	2404280-7
12.5	15.83	17.5	6	2404280-6
10.0	13.33	15.0	5	2404280-5
7.5	10.83	12.5	4	2404280-4
5.0	8.33	10.0	3	2404280-3
2.5	5.83	7.5	2	2404280-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.30
2 PLC ±0.20
3 PLC ±-
4 PLC ±-
ANGLES ±3°

MATERIAL △1

FINISH -
-

DWN W. HUO 06DEC2021
CHK L. CHEN 07DEC2021
APVD D. ZHANG 08DEC2021
PRODUCT SPEC 108-2418
APPLICATION SPEC 114-13315
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME HEADER ASSEMBLY, VERTICAL GLOW WIRE, WITH BOSS, EP2.5
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2404280	-

SCALE N/A SHEET 2 OF 2 REV A1

Downloaded from Arrow.com.