NS 35/ 7,5 UNPERF 250MM - DIN rail, unperforated

1207647

https://www.phoenixcontact.com/us/products/1207647

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver-colored

Commercial data

Item number	1207647
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	BH8422
GTIN	4046356366052
Weight per piece (including packing)	90.37 g
Weight per piece (excluding packing)	90.37 g
Country of origin	DE


Downloaded from Arrow.com.

Technical data

Product properties

Product type	DIN rail

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	0 mm
Height	7.5 mm
Hole height	0 mm
Length	250 mm
Drill hole spacing	0 mm

Material specifications

Color	silver-colored
Material	Steel
Coating	galvanized, passivated with a thick layer

Standards and regulations

Tests	acc. to EN 60715

Electrical tests


Short-time withstand current


Equivalent E-Cu cross-section	16 mm²
Short-time current resistance 1s	1.92 kA

Downloaded from Arrow.com.

Drawings

Dimensional drawing





Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 9.0	EC001285

UNSPSC

UNSPSC 21.0	39121700

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com

Downloaded from Arrow.com.