




APPROVED: _____
 DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/18/20	



2*3PIN VIEW



2*2PIN VIEW



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Nature

Electrical:

Current rating: 3A AC/DC

Contact resistance: 20 Mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02x2 thru 20x2

A= .079 [2.00] x No. of Space

B= .079 [2.00] x No. of Space + .154 [3.90]

C= .079 [2.00] x No. of Space + .093 [2.35]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	OW	3/18/20
CHECKED	MY	3/18/20
APPROVED		

**ADAM
 TECH**
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		.079 [2.00] HOUSING	
SIZE	PART NO.	REV.	
X	2CHD-C2-XX-V0	-	
REF: S00124T	SCALE: NTS	SHEET 1 OF 1	