





REV.	DATE	DESCRIPTION
NC	07/11/00	INITIAL RELEASE



*Crimp Ferrule
Hex CR Size .213*

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN () ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS	DATE	 SMA REVERSE POLARIZED CRIMP JACK (FOR TIMES LMR-200)						
1 BODY	BRASS	GOLD	DRAWN	G.R.S.	07/11/00		TITLE SMA REVERSE POLARIZED CRIMP JACK (FOR TIMES LMR-200)						
2 INSULATOR	TEFLON	NATURAL	CHECKED										
3 CONTACT PIN	BRASS	GOLD	ISSUED										
4 FERRULE	COPPER	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4			SIZE							
5						FSQM NO.		99001		DWG. NO.	132236RP.DWG	REV.	NC
6						SCALE		NA		PART NO.	132236RP	SHEET	1 OF 1
7													
8			DO NOT SCALE DRAWING										