

## Han-Eco reducer gasket 12-20mm M40



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 41 000 5142  |
| Specification      | Han-Eco reducer gasket 12-20mm M40  |
| HARTING eCatalogue | <a href="https://harting.com/19410005142">https://harting.com/19410005142</a> |

### Identification

|                          |                       |
|--------------------------|-----------------------|
| Category                 | Accessories           |
| Series of hoods/housings | Han-Eco®              |
| Type of accessory        | Reduction seal insert |

### Technical characteristics

|                |              |
|----------------|--------------|
| Size           | M40          |
| Clamping range | 12 ... 20 mm |

### Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| Colour (accessories)                 | RAL 9005 (jet black) |
| RoHS                                 | compliant            |
| ELV status                           | compliant            |
| China RoHS                           | e                    |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Not contained        |

### Commercial data

|                                |          |
|--------------------------------|----------|
| Packaging size                 | 10       |
| Net weight                     | 8 g      |
| Country of origin              | Germany  |
| European customs tariff number | 40169300 |



**Pushing Performance**  
Since 1945

## Commercial data

|             |  |
|-------------|--|
| GTIN        | 5713140130555                              |
| eCl@ss      | 27140807 Additional components cable gland |
| ETIM        | EC003608                                   |
| UNSPSC 24.0 | 39121431                                   |