



Part Number : [1300970165](#)

Product Description : Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625")

Series Number : 130097

Status : Active

Product Category : Cable Grips

Engineering Number : 36256



Documents & Resources

Drawings

[Drawing 1300970165_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Cable Grips
Series	130097
Description	Deluxe Cord Grips Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625")
Hazardous Locations	Class I, Div. 2, Class II, Div. 1 and 2, Class III, Div. 1 and 2
NEMA Rating	NEMA 4
Product Family	Strain-Relief Cord Grips
Product Name	Deluxe Cord
Type	Strain Relief Grip
UPC	78678836256

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	0.089m (3.50")
Body Style	Straight
Cable Diameter	12.70-15.88mm (.500-.625")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Aluminum
Material - Grip	Stainless Steel
Mesh Length	0.178m (7.00")
Number of Holes	N/A
O-Ring	N/A

Thread Size	1/2" NPT
-------------	----------

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Sep 22, 2024
