

Docking Frame for 4 modules, fixed mount




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 016 1711
Specification	Docking Frame for 4 modules, fixed mount
HARTING eCatalogue	https://b2b.harting.com/09140161711

Identification

Category	Accessories
Series	Han-Modular®
Type of accessory	Docking frame
Description of the accessory	Fixed for 4 modules a ... d

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Mating cycles with other HMC components	≥10,000
Degree of protection acc. to IEC 60529	IP20
Lock-in range	±4 mm

Material properties

Material	Polycarbonate (PC)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	2
Net weight	25 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440206 Module carrier frame for industrial connectors