

## PRODUCT SELECTOR

PRODUCT TYPE	POSITIONS	IP RATING	AMPERAGE	HOUSING MATERIAL	PRODUCT LINE
<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>
VOLTAGE					
<input style="border: 1px solid #ccc; padding: 2px 10px;" type="button" value="Search All"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #ccc; padding: 2px 10px; background-color: #ccc; color: #ccc; font-weight: bold; font-size: 0.9em;" type="button" value="RESET"/> <span style="border: 1px solid #0070C0; color: #0070C0; padding: 0 5px;">▼</span>	<input style="border: 1px solid #0070C0; color: #0070C0; padding: 2px 10px; font-weight: bold; font-size: 0.9em;" type="button" value="SEARCH"/>			



Home &gt; Our Product Lines &gt; RADSOOK &gt; mate &gt; busbar &gt; N021006601002 Radsok® 10 mm contact with thread M10

## N021006601002 RADSOOK® 10 MM CONTACT WITH THREAD M10

PART NUMBER: N021006601002

[DATASHEET](#) View / Download

### SPECIFICATIONS:

**Version:** Screw**Contact Size:** 10mm**Housing Part #:** N 02 100 6601 002**Mating Cycles:** 1000**Thread:** M10**Torque:** 15 Nm**Mating Part(s):** N 02 100 6601 002

### QUANTITY

1

REQUEST A QUOTE

 Like [Sign Up](#) to see what your friends like. Like [Sign Up](#) to see what your friends like.

### DESCRIPTION

Radsok® 10 mm contact with thread M10

### RELATED ITEMS



N020606601002 Radsok® 6 mm  
contact with thread M6



N020806601002 Radsok® 8 mm  
contact with thread M8



N021006601002 Radsok® 10 mm  
contact with thread M10

#### LINKS

- [Company](#)
- [Contact](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [Code of Business Conduct and Ethics](#)
- [ISO Certification](#)
- [Quality Policy](#)
- [Industrial@Amphenol News](#)
- [Test Reports](#)

#### SHOP

- [Our Product Lines](#)
- [Market Applications](#)
- [Distributors](#)

#### FOLLOW US!

