


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	250 kcmil
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-5/16 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90 ° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	YELLOW
Panduit Die Index No. on Barrel	P62
Alternate Industry Die Index No. () on Barrel	(16)



CERTIFIED LISTED
Wire Connector



				PANDUIT CORP. TINLEY PARK, ILLINOIS			
				LCAN250-38-X			
				Copper Lug - One-Hole, Narrow Tongue, Standard Barrel			
REV	DATE	BY	CHK	DESCRIPTION		ECN	SCALE N/A
01	11/08	DRL	DRL	TONGUE THICKNESS WAS .14 $\pm$.01			
				DRAWING NO / CAD FILE		LCAN250-38-CUST	