Data sheet

MOFU 15/35 ZDUB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Accessories, Mounting foot
Order No.	1723660000
Type	MOFU 15/35 ZDUB
GTIN (EAN)	4008190975531
Qty.	50 items

Downloaded from Arrow.com.

Data sheet

MOFU 15/35 ZDUB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	43 mm	Height (inches)	1.6929 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	1.04 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	For the mounting rails	End cover plate required	Yes
Mounting rail	TS 35, TS 15		

Additional technical data

Open sides	right	Type of fixing	Snap-on
Explosion-tested version	No	Type of mounting	Plugged

Conductors for clamping (rated connection)

Connection direction	top	Type of connection	Tension-clamp connection

Dimensions

Pitch in mm (P)	18.00 mm	TS 15 offset	21 mm
TS 35 offset	2 mm		

General

Mounting rail	TS 35, TS 15

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Downloaded from Arrow.com.