


6		5	4	3	2	1
PART NUMBER	TITLE		CABLE DESCRIPTION		LENGTH 'L'	CABLE COLOR
2175211121	MIZU-P25 F-S 75MM 0.5 SQMM LEAD BK Sn		1CX0.5 SQMM DISC PVC BK FLRY-B		75±3	BLACK
2175211122	MIZU-P25 F-S 150MM 0.5 SQMM LEAD BK Sn		1CX0.5 SQMM DISC PVC BK FLRY-B		150±5	BLACK
2175211123	MIZU-P25 F-S 225MM 0.5 SQMM LEAD BK Sn		1CX0.5 SQMM DISC PVC BK FLRY-B		225±5	BLACK
2175211124	MIZU-P25 F-S 300MM 0.5 SQMM LEAD BK Sn		1CX0.5 SQMM DISC PVC BK FLRY-B		300±5	BLACK
2175211125	MIZU-P25 F-S 450MM 0.5 SQMM LEAD BK Sn		1CX0.5 SQMM DISC PVC BK FLRY-B		450±5	BLACK
2175212121	MIZU-P25 F-S 75MM 0.5 SQMM LEAD RD Sn		1CX0.5 SQMM DISC PVC RD FLRY-B		75±3	RED
2175212122	MIZU-P25 F-S 150MM 0.5 SQMM LEAD RD Sn		1CX0.5 SQMM DISC PVC RD FLRY-B		150±5	RED
2175212123	MIZU-P25 F-S 225MM 0.5 SQMM LEAD RD Sn		1CX0.5 SQMM DISC PVC RD FLRY-B		225±5	RED
2175212124	MIZU-P25 F-S 300MM 0.5 SQMM LEAD RD Sn		1CX0.5 SQMM DISC PVC RD FLRY-B		300±5	RED
2175212125	MIZU-P25 F-S 450MM 0.5 SQMM LEAD RD Sn		1CX0.5 SQMM DISC PVC RD FLRY-B		450±5	RED



ITEM	PART#	DESCRIPTION	QTY	UOM
A	501488000	2.5 W.P. CONN CRIMP PIN	1	PC

NOTES:

1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
2. THE PRODUCT SPECIFICATION RELIES ON TERMINAL AND WIRE SPEC.
2. FREE END MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1MM. TINNING DIA MUST BE 1.25MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
18/01/2021	A	INITIAL RELEASE	ARAJU

DOCUMENT STATUS	P1	RELEASE DATE	2021/01/19	03:54:21
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		NTS												
	F A = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				SEE TABLE									
F E = 0	ANGULAR TOL ± °														
F D = 0	4 PLACES ±														
DIVISIONAL SYMBOLS	3 PLACES ±				EC NO: 653327		2021/01/18		PRODUCT CUSTOMER DRAWING						
	2 PLACES ±				DRWN: ARAJU		2021/01/19								
	1 PLACE ±				CHK'D: RDESAI01		2021/01/19								
	0 PLACES ±				APPR: RDESAI01		2021/01/19								
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				INITIAL REVISION:		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION		
					DRWN: ARAJU		2021/01/18		2175211121		PSD		000		A
				APPR: RDESAI01		2021/01/19									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A4-SIZE		217521		SEE TABLE		GENERAL MARKET		1 OF 1	