

Part Number : [1300250087](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, Gray DeviceNet Thick (Trunk) Cable, 12.0m (39.37') Length

Series Number : 130025

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : DN11A-M120



Documents and Resources

Drawings

[1300250087_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130025
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, Gray DeviceNet Thick (Trunk) Cable, 12.0m (39.37') Length
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Double Ended
UPC	78678837836

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	12.10mm (.480")
Cable Length	12.0m (39.37')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded

Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	2449.396/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +60°C
Wire/Cable Type	Thick (Trunk)
Wire Size (AWG)	15, 18

This document was generated on Jun 17, 2026