T 3328 504 U





Data Overview

Description:	Female Coupling Plug; 4 Pin; Solder; Silver; 4-6mm; IP40
rated voltage	300 V
number of positions (w/o PE)	4
rated current (40 °C)	10 A
termination	solder pin
contact plating	silver
IP-class mated	IP40
Product Availability	Currently not on stock
Packing Unit:	**100 Pieces**
Min. Order Quantity:	**100 Pieces**
Price per Piece:	**€4.27**
Total Price plus VAT:	**€427.00**

Send Request

100 Add to Cart

Stock of our Distributors

Technical Data

General Characteristics

part category	coupling receptacle
gender	female
locking system	bayonet ring
housing style	straight
minimum cable diameter	4 MM
maximum cable diameter	6 MM
lower temperature	-40 GC
upper temperature	100 GC
IP-class mated	IP40

Electrical Characteristics

Further Characteristics

Downloads

Frequently Asked Questions

- Which components belong to a complete bill of materials (BOM)?
- Amphenol as a supplier of complete assemblies and plug & play solutions
- What options are there for direct transfer to a printed circuit board?
- How does the transmission of the cable shielding work with M16B connectors?
- Crimping or soldering - what are pros & cons?
- Tarnishing of silver-plated contacts - what's the reason?
- What options are there for color adjustments to the application?
- M16 receptacles with hex nut instead of ring nut?
- What are the 5 and 7 pole stereo layouts used for?
- What does the U at the end of the part number stand for?

This might interest you



Accessory »



Housing »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

Newsletter

E-Mail

I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following consent.

Subscribe to Newsletter

© Amphenol Tuchel Industrial GmbH 2026

Powered by Arrow.com