


© 2016 TE Connectivity, All Rights Reserved.


REVISIONS
変更


P	LTR	DESCRIPTION	DATE	DWN	APVD
	M10	REVISED ECR-25-257352	08OCT2025	AY	KY















1. X 面から2mmの範囲で測定
2. 嵌合相手ハウジング型　174515, 174516, 917989, 917992
3. 推奨取付ねじ：JIS　B1115, B1112　タッピンねじ，なべ2種
   呼び径3，長さ6mm以下（締付けトルク：39N・cm（4kgf-cm）以下）
4. 適用製品規格番号：108-5280, 108-5342
5. 回路番号：
   パワー回路　①～⑯
   シグナル回路　⑰～㊽



6. コンタクト仕上識別マーク

1. MUST BE KEPT BETWEEN X AND 2
2. THE MATING PLUG HSG.PART NUMBER;174515, 174516, 917989,917992
3. RECOMMENDED MOUNTING SCREW,3mmDIA,6mmLENGTH(MAX.)
   PAN HEAD,CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115,B1122
   (TIGHTENING TORAUE;39.2N・cm(4kgf・cm)MAX.)
4. APPLICABLE PRODUCT.SPEC NO ; 108-5280, 108-5342
5. CIRCUIT NUMBER
   POWER CIRCUIT NO.　①～⑯
   SIGNAL CIRCUIT NO.　⑰～㊽
6. MARKING FOR DISCERNMENT OF THE CONTACT FINISH

		SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	COLOR 色	PART NUMBER 製品型番
	54	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16 PRE-TIN × 32		33~40, 41~48	YELLOW 黄色	4-5174917-7
	57	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 5 PRE-TIN × 43	-	19, 20, 27, 28, 36	GRAY 灰色	7-5174917-6
OBSOLETE	56	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 7 PRE-TIN × 41		21~23, 28~31	YELLOW 黄色	6-5174917-7
	58	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 10 PRE-TIN × 38	-	19, 20, 22, 28~32, 36, 44	GRAY 灰色	8-5174917-6
OBSOLETE	59	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8 SELECTIVE-TIN (BRIGHT) × 40		19, 20, 27~31, 36	GRAY 灰色	9-5174917-6
OBSOLETE	55	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8 SELECTIVE-TIN (BRIGHT) × 40		33~40	YELLOW 黄色	5-5174917-7
OBSOLETE	52	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 15 SELECTIVE-TIN (BRIGHT) × 33		18~24, 27~32, 36, 44	YELLOW 黄色	2-5174917-7
OBSOLETE	8	TIN-LEAD	SELECTIVE GOLD × 10 PRE-TIN × 38		19, 20, 22, 28~32, 36, 44	GRAY 灰色	8-174917-6
SUPERSEDED BY 7-5174917-6	7	TIN-LEAD	SELECTIVE GOLD × 5 PRE-TIN × 43		19, 20, 27, 28, 36	GRAY 灰色	7-174917-6
	4	TIN-LEAD	SELECTIVE GOLD × 16 PRE-TIN × 32	-	33~40, 41~48	YELLOW 黄色	4-174917-7
OBSOLETE	3	TIN-LEAD	SELECTIVE GOLD × 16 PRE-TIN × 32		17~24, 33~40	NATURAL 自然色	3-174917-1
	2	TIN-LEAD	SELECTIVE GOLD × 15 PRE-TIN × 33	-	18~24, 27~32, 36, 44	YELLOW 黄色	2-174917-7
OBSOLETE	0	PRE-TIN × 48				ORANGE オレンジ色	174917-8
	0	PRE-TIN × 48		-	-	YELLOW 黄色	174917-7
	0	PRE-TIN × 48		-	-	GRAY 灰色	174917-6
OBSOLETE	0	PRE-TIN × 48				BLUE 青色	174917-5
	0	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT) × 48	-	-	NATURAL 自然色	174917-2
	0	PRE-TIN × 48		-	-	NATURAL 自然色	174917-1

A MARKING マーキング　CONTACT FINISH コンタクト仕上　A GOLD PLATED CIRCUIT NO. 金めっき回路番号

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位：特 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差
0 PLC ±
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

GENERAL TOLERANCE
0<< 10 : ±0.2
10<< 30 : ±0.25
30<<100 : ±0.3
ANGLES : ±3°

MATERIAL 材料: HOUSING: PBT
CONTACT: BRASS

FINISH 仕上: –

DWN T.SHINOHARA 08FEB08
CHK K.BETSUI 08FEB08
APVD K.BETSUI 08FEB08
PRODUCT SPEC 製品規格: SEE NOTE 4
APPLICATION SPEC 取付適用規格: —
WEIGHT: 0.000000

TE Connectivity

NAME 名称
48POSITION CAP HOUSING ASSEMBLY
040/070 SERIES HYBRID I/O CONNECTOR

SIZE A1 | CAGE CODE 00779 | DRAWING NO 番号 C-174917 | RESTRICTED TO —

CUSTOMER DRAWING | SCALE 尺度 2:1 | SHEET 1 OF 1 | REV M10

Downloaded from Arrow.com.