



Part Number : [1301530084](#)

Product Description : Super-Safeway Right-Angle Industrial GFCI, Portable, Single Phase, Automatic Reset, Outlet Box, NEMA 5-15 Double Duplex with Flip Lids, 15A, 120V, 0.61m (2.0') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Number : 15053W-2A



Documents & Resources

Drawings

[1301530084_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway Right-Angle Industrial GFCI, Portable, Single Phase, Automatic Reset, Outlet Box, NEMA 5-15 Double Duplex with Flip Lids, 15A, 120V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 3R
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678888272

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
GFCI Reset	Automatic
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	125V

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')

Cord Type	12/3 SJTW
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Sep 16, 2025