

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301030021

Status:

Active

Overview:

Description:

Watertite Wet Location Incandescent Hand Lamp Only, 100W with Screw Release
Ungrounded Vinyl Guard

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130103
NEMA Configuration	N/A
NEMA Rating	NEMA 4X
Outlet	None
Overview	hand_lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678861293
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Insulated, Screw Release
Height	457.20mm (18.000")
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC
Material Info	
Engineering Number	1203I

Search Parts in this Series

130103 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION