Twist-Lock® Devices
15A, 250V, 2 Pole, 3 Wire Grounding
Receptacle

HUBBELL

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip



15A 250V
NEMA L6-15R
UL/CSA



Ordering Information

Description	Device Color	UPC	Catalog Number
Single, panel mount, black nylon face, side wired only	Black	783585236629	HBL4563

Listings

Listed to UL 498
Fed. Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Face	RTP
Base	RTP
Contacts	Brass
Clamp	Brass
Ground Contact	Brass
Terminal Screws	Brass

Performance

Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Terminal Accommodation	#18 AWG - #10 AWG solid or stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498

Environmental

Flammability	HB or better per UL94/CSA 22.2 No.0.17
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Plug	HBL4570C

Resources

Customer Use Drawing
eCatalog

Dimensions in Inches (mm)

Downloaded from Arrow.com.

HUBBELL®
Wiring Device-Kellems