



Part Number : [1062920505](#)

Product Description : MMC Female-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable

Series Number : 86170

Status : Active

Product Category : Fiber Optic Cable Assemblies



Documents and Resources

Drawings

[1062920505_sd.pdf](#)

Specifications

[1062920301-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86170
Description	MMC Female-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable
Connector to Connector	MMC-to-(2) MPO
Mode	Singlemode
Product Name	MMC,MPO
UPC	198282258834

Physical

Boot Type	Straight
Cable Length	5.0m
Cable Size	2.50mm, 3.00mm
Fiber (Core/Cladding)	9/125µm
Net Weight	1.000/g
Single Ended	No
Wire/Cable Type	16 Fiber Bend-insensitive Plenum