HellermannTyton

Technical data sheet

Article number:
115-06219 **RT40R**

Product Group	Releaseble Cable Ties
Product Family	RT Series With Extended Pawl
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)

Bundle Diameter max (metric)	51.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Length (L)	215.9 mm
Min.Tensile Strength	180 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	Yes
Specifications	UL-ZODZ2.E64139
Thickness (T)	1.2 mm
UL-File Number	E64139
Variant	Inside Serrated
Weight/Unit	0.0012 kg
Width (W)	4.0 mm

RoHS

c UL us

created on 6. September 2024, 6:50 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.