
Part Number : 1300940440
Product Description : Heavy Duty Support Grip, Double Eye, Double Weave, Closed Mesh, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 1224.70kg (2700 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Part Number : 35425



Documents and Resources

Drawings

PK-130227-004-001.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Heavy Duty Support Grip, Double Eye, Double Weave, Closed Mesh, Cable Diameter 19.05-25.15mm (.750-.990"), Approximate Break Strength 1224.70kg (2700 lbs)
Product Name	Heavy Duty
Type	Support Grip
UPC	78678835425

Agency

CSA	LR32159

Physical

Approximate Break Strength	1224.70kg (2700 lbs)
Bale Length	0.254m (10.00")
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Double
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.66m (26.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Downloaded from Arrow.com.