

# MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY  
FREDERICK, ILLINOIS

FED. MFR. CODE 91929

## ACTUATOR - SWITCH

CATALOG LISTING

JS - 3

(M) JS-3  
ISSUE 3

REPLACES

RELEASE NO.

JS-3

M

DRAWING  
NUMBER

ISSUE

7

CHECK

REVISIONS

A CO 12901

K L B

25 MAY 59

B CO 17304

M S F

4 DEC 63

C CO47771

C J H

17 MAY 80

D CO79303

D L T

7 MAR 95

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK



CHECK

CHECK


2-56 NC X .500 REF ROUND HEAD MACHINE SCREW (2)

2-56 NC HEX NUT (2)

LOCKWASHER (2)



CORROSION RESISTANT  
STEEL ACTUATOR



DOTTED LINES INDICATE  
BASIC SWITCH IN PLACE

NOTE -

- FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

### CHARACTERISTICS WITH ISMI BASIC SWITCH INSTALLED

OPERATING FORCE ----- 10 OZ MAX

RELEASE FORCE ----- 2 OZ MIN

DIFFERENTIAL TRAVEL ----- .020 MAX

OVERTRAVEL ----- .015 MIN

### ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE  
SPECIFIED  
DIMENSIONS ARE IN INCHES

### TOLERANCES ARE:

|             |        |        |
|-------------|--------|--------|
| ONE PLACE   | (.0)   | ± .030 |
| TWO PLACE   | (.00)  | ± .015 |
| THREE PLACE | (.000) | ± .005 |
| ANGLES      |        | ± 2°   |

WEIGHT

FO-50378

DRAWN

K L B

25, MAY '59

CHECK

CHECK

CHECK

CHECK

CHECK