









| REVISIONS |     |                            |           |     |      |
|-----------|-----|----------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION                | DATE      | DWN | APVD |
|           | A   | RELEASED PER ECO-21-003568 | 16MAR2021 | KM  | CG   |
|           |     |                            |           |     |      |
|           |     |                            |           |     |      |





- ⚠ MATERIAL: HOUSINGS; LCP, COLOR-NATURAL CONTACT; BERYLLIUM COPPER SOLDER BALL; SEE TABLE TAPE, FILM; KAPTON WITH SILICON ADHESIVE
- ⚠ FINISH: CONTACT; GOLD (SEE TABLE) ON MATING AREA OVER NICKEL ON ENTIRE CONTACT.
- 3. PRODUCT IS PACKAGED ON TAPE AND REELED.
- ⚠ DIAGRAM REPRESENTS THE DE-REELING DIRECTION OF THE PACKAGED CONNECTORS.




|                    |    |                         |                        |           |                      |             |
|--------------------|----|-------------------------|------------------------|-----------|----------------------|-------------|
| 2102060-2          | 24 | 17                      | 1.27 µm                | 13        | LEAD FREE PER SAC405 | 1-2355825-8 |
| 2102060-1          | 24 | 17                      | 1.27 µm                | 13        | TIN LEAD             | 1-2355825-7 |
| 2102060-2          | 24 | 18                      | 1.27 µm                | 14        | LEAD FREE PER SAC405 | 1-2355825-0 |
| 2102060-1          | 24 | 18                      | 1.27 µm                | 14        | TIN LEAD             | 2355825-9   |
| 2102060-2          | 20 | 12                      | 1.27 µm                | 8         | LEAD FREE PER SAC405 | 2355825-4   |
| 2102060-1          | 20 | 12                      | 1.27 µm                | 8         | TIN LEAD             | 2355825-3   |
| 2102060-2          | 20 | 10                      | 1.27 µm                | 6         | LEAD FREE PER SAC405 | 2355825-2   |
| 2102060-1          | 20 | 10                      | 1.27 µm                | 6         | TIN LEAD             | 2355825-1   |
| MATING PART NUMBER | T  | MATED STACK HEIGHT (mm) | GOLD PLATING THICKNESS | H MAX REF | SOLDER BALL MATERIAL | PART NUMBER |

|                                        |  |                                                                                                               |                                    |                                                                              |  |
|----------------------------------------|--|---------------------------------------------------------------------------------------------------------------|------------------------------------|------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>A. MILLER<br>CHK<br>C. GINGRICH<br>APVD<br>K. THACKSTON                                                | 18DEC2019<br>18DEC2019<br>6MAR2021 | TE Connectivity                                                              |  |
| DIMENSIONS:<br>mm                      |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±0.13<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |                                    | NAME<br>ASSEMBLY, SOCKET, 114 POSITION, MEZALOK STACKING CONNECTOR LOW-FORCE |  |
| MATERIAL                               |  | FINISH                                                                                                        |                                    | SIZE<br>A1                                                                   |  |
| ⚠                                      |  | ⚠                                                                                                             |                                    | CAGE CODE<br>108-160206                                                      |  |
| CUSTOMER DRAWING                       |  | DRAWING NO.<br>114-13279                                                                                      |                                    | RESTRICTED TO<br>A1                                                          |  |
| SCALE 8:1                              |  | SHEET 1 OF 2                                                                                                  |                                    | REV A                                                                        |  |

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| P         | LTR | DESCRIPTION | DATE | DWN | APVD |
| -         | -   | SEE SHEET 1 | -    | -   | -    |
|           |     |             |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |



|                                                                                       |                                                                               |                                                             |                                                                                                       |               |
|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------|-------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                                                               | DWN<br>K. MILLER<br>18DEC2019                               |  TE Connectivity |               |
| DIMENSIONS:                                                                           |                                                                               | CHK<br>C. GINGRICH<br>18DEC2019                             |                                                                                                       |               |
| mm                                                                                    | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                        | APVD<br>K. THACKSTON<br>16MAR2021                           | NAME                                                                                                  |               |
|  | 0 PLC ±<br>1 PLC ±<br>2 PLC ±0.13<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±<br>FINISH | PRODUCT SPEC<br>108-160206<br>APPLICATION SPEC<br>114-13279 | ASSEMBLY, SOCKET, 114 POSITION,<br>MEZALOK STACKING CONNECTOR<br>LOW-FORCE                            |               |
| MATERIAL                                                                              | -                                                                             | WEIGHT                                                      | SIZE                                                                                                  | RESTRICTED TO |
| -                                                                                     | -                                                                             | -                                                           | A100779C=2355825                                                                                      | -             |
| -                                                                                     | -                                                                             | CUSTOMER DRAWING                                            | SCALE                                                                                                 | REV           |
| -                                                                                     | -                                                                             | -                                                           | 8:1                                                                                                   | A             |