
**Part Number :** 154661424
**Product Description :** 0.50mm Pitch Premo-Flex FFC Jumper with Latching Ears, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 24 Circuits
**Series Number :** 15466
**Status :** Active
**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

154661424_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

154660001-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2023)8585-DC (23 Jan 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Flat-Flexible Cable (FFC) |
| Series | 15466 |
| Description | 0.50mm Pitch Premo-Flex FFC Jumper with Latching Ears, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 24 Circuits |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 196823198397 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

### Physical

| | |
|---|---|
| Cable Length | 102.00mm |
| Circuits (Loaded) | 24 |
| Contact Layout Type | D (opposite side) |
| Design Feature | Superior Retention |
| Material - Plating Mating | Tin |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.50mm |
| Temperature Range - Operating | -40° to +105°C |
| Termination Style | FFC Connector |

Downloaded from Arrow.com.

| | |
|---|---|
| Wire/Cable Type | Flat Flexible Cable (FFC) |
| Wire Size (AWG) | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Easy-On FFC/FPC Connector, 0.50mm Pitch, 1.90mm Height, Single Bottom Contact (FS19), Right-Angle, Surface Mount, ZIF, 24 Circuits, Tin-Bismuth Plating | 5052782470 |



Downloaded from Arrow.com.