Part Number : 1200688219
Product Description : Brad Safety Micro-Change (M12) Drop Wye, 4 Poles, A-Coded, Female/Female with Male Drop
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : SAFESPLIT000



Documents and Resources

Drawings

1200688219_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Brad Safety Micro-Change (M12) Drop Wye, 4 Poles, A-Coded, Female/Female with Male Drop
IP Rating	IP67
Product Name	Brad Safety,Micro-Change (M12)
Type	Drop Wye
UPC	889056564021

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	A-Coded
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Net Weight	33.664/g
Poles	4
Right Trunk Connector	Micro-Change (M12)

Downloaded from Arrow.com.

Right Trunk Gender	Female
Temperature Range - Operating	-25° to +90°C

Downloaded from Arrow.com.