



Part Number : [734152061](#)
Product Description : MMCX Jack, Straight,
PCB Receptacle, Surface Mount, Brass Body,
Gold (Au) Plating, Tray, 50 Ohms
Series Number : 73415
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings
[734152061_sd.pdf](#)

3D Models and Design Files
[734152061_stp.zip](#)

Specifications
[PS-89675-1920-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	MMCX Jack, Straight, PCB Receptacle, Surface Mount, Brass Body, Gold (Au) Plating, Tray, 50 Ohms
Product Name	MMCX
Style	PCB
Type	Microminiature
UPC	756054217467

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.230/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on Apr 26, 2025
