

Mini DisplayPort to HDMI Adapter Cable, Active, M/M, 3 ft. (0.91 m)

MODEL NUMBER: **P586-003-HDMI**



Connects the Mini DisplayPort™ (mDP) on your computer or laptop to an HDMI monitor, projector or television.

Features

Send High-Definition Mini DisplayPort Audio/Video Signals to an HDMI Display

- Connects mDP computer to HDMI-enabled monitor, projector or TV
- Ideal for displaying video on a large monitor or digital sign
- No separate power adapter required

Vibrant Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Supports audio and HDCP
- Designed for Dual-Mode DP++ graphics cards

Superior Materials for Superior Performance

- Gold-plated HDMI connector and nickel-plated mDP connector for excellent conductivity
- Integral strain relief for long life

Specifications

OVERVIEW	
UPC Code	037332200495
Technology	HDMI; DisplayPort

Highlights

- Supports video resolutions up to 1920 x 1080 (1080p)
- Supports audio and HDCP
- No separate power adapter required
- Designed for Dual-Mode DisplayPort++ graphics cards
- Gold-plated HDMI connector

System Requirements

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P586-003-HD-V2A

Package Includes

- P586-003-HDMI Mini DisplayPort to HDMI Adapter Cable (M/M), 3 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p)
Max Supported Color Depth	12-bit True Color
Chroma Sub Sampling	4:4:4
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.8mm
Wire Gauge (AWG)	32
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / cm)	1.27 x 11.43 x 9.91
Shipping Dimensions (hwd / in.)	0.50 x 4.50 x 3.90
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Operating Humidity Range	10 to 85%, Non-Condensing
Storage Humidity Range	5 to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold; Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1a
HDCP Specification	1.3
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>