

## USB-C Cable (M/M), USB 2.0, 5A (100W) Rated, USB-IF Certified, 2M (6.6 ft)

MODEL NUMBER: U040-C2M-C-5A



Provides up to 20V 5A (100W) for powering and charging your MacBook Pro or other mobile device through a USB-C charger or power bank.

### Features

**USB-C to USB-C Cable Connects 2 USB-C Devices, Including MacBooks and Smartphones** This two-meter USB Type-C to Type-C cable allows you to connect one USB-C device to another. For instance, a laptop to a docking station, your smartphone to a wall charger, or a hard drive or flash drive to a computer or tablet. The USB-C to C cable is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks.

**PD Charging Cable Produces up to 100W for Rapid Syncing and Charging** The Power Delivery cable provides power output up to 5 amps (100 watts), which is sufficient for fast-charging, syncing and powering most large-capacity devices, including the MacBook Pro. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB Type-C to USB Type-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

**Reversible USB-C Connectors Attach in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

**USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance** This cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U040-C2M-C-5A meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

## Specifications

| OVERVIEW   |                      |
|------------|----------------------|
| UPC Code   | 037332241306         |
| Technology | USB 2.0 (High Speed) |

### Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Power Delivery cable provides 5A (100W) for fast-charging large-capacity devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-C wall charger up to 2 m away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports

### Package Includes

- U040-C2M-C-5A USB-C to USB-C Cable, USB-IF, M/M, 2 m

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Cable Type                           | Passive                             |
| <b>PHYSICAL</b>                      |                                     |
| Material of Construction             | PVC                                 |
| Cable Jacket Color                   | Black                               |
| Cable Jacket Rating                  | VW-1                                |
| Cable Outer Diameter (OD)            | 4.0MM                               |
| Cable Length (ft.)                   | 6.6                                 |
| Cable Length (m)                     | 2.01                                |
| Cable Length (in.)                   | 78.7                                |
| Cable Length (cm)                    | 200                                 |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50                  |
| Shipping Weight (kg)                 | 0.04                                |
| Unit Packaging Type                  | Polybag                             |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)         |
| Storage Temperature Range            | -4° to 185°F (-20° to 85°C)         |
| Relative Humidity                    | 10% to 85%, Non-Condensing          |
| <b>CONNECTIONS</b>                   |                                     |
| Side A - Connector 1                 | USB C (MALE)                        |
| Side B - Connector 1                 | USB C (MALE)                        |
| Connector Plating                    | Nickel                              |
| Contact Plating                      | Gold                                |
| Connector Style                      | Straight                            |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| USB Specification                    | USB 2.0 (up to 480 Mbps)            |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Certifications               | USB-IF                              |
| Product Compliance                   | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |
| Product Warranty Period (Worldwide)  | 3-year limited warranty             |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.