


FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

CATALOG LISTING

YA-2RQ1243-D6

ADM9700

SWITCH - BASIC




NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA
ON 1.000±.002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURES OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - -14-22 OZ

RELEASE FORCE - - - - 10 0Z MIN

DIFFERENTIAL TRAVEL ---.0020-.0075

OVERTRAVEL — — — — —.219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

20A-125, 250 OR 480 VAC; 10A-125 VAC "L"
1HP-125 VAC; 2HP-250 VAC
CODE L23 1/2A-125 VDC; 1/4A-250 VDC

L288
L308
L315



20(3)A 250V T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/04		
ONE PLACE	X,X	0,4/018	X,X	0,8/03
TWO PLACES	X,X,X	0,15/008	X,X,X	0,38/015
THREE PLACES			X,X,X,X	0,13/005
ANGLES				

SI METRIC

US CUSTOMARY

DESIGN UNITS

☒ CUSTOMARY

WEIGHT	.093 LB
--------	---------

YA-2RQ1243-D6

CATALOG LISTING

Σ

8

REVISIONS

A	C062204 WJK 28 OCT 87
B	CO- 77588 KDR 29 MAR 94
C	CO 80938 DLT 7 JUN 95
D	C092958 JAS 15 MAY 98
E	C093346 DLT 27 AUG 98
F	0000831 CSL 10 JUL 03
G	0017742 TSG 09JAN06

RASTER

DRAWN

R J H	29 JUN 82	CHECK CEB
-------	-----------	-----------