



Part Number : [1301050041](#)

Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer TEFLON Globe with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length

Series Number : 130105

Status : Active

Product Category : Lamps and Lights

Engineering Part Number : 1625-12A



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130105
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer TEFLON Globe with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps, Specialty Light
UPC	78678862504

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Cord Type - Primary	16/3 SOOW

Cord Type - Secondary	14/2 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Teflon*
Material - Guard	N/A
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Apr 28, 2026