



Part Number : [1301080173](#)
Product Description : Watertite Wet Location
13W Fluorescent Hand Lamp with Switch,
Cord Type 16/3 SJTOOW, Cord Length 15.24m
(50.0')
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1913SB



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130108
Description	Watertite Wet Location 13W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJTOOW, Cord Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Wide-Area Lighting Products
Product Name	Watertite
Type	Wide Area Lamps
UPC	78678829023

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOOW
Depth	69.85mm (2.750")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	PL13/41
Length	444.50mm (17.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held

Outlet	None
Packaging Type	Carton

This document was generated on Sep 30, 2023