

Active

PRODUCT DRAWING
English

3D PDF

See All Documentation

TE CONNECTIVITY (TE)

KCS01X024EACA=CONTACTOR,CURRENT SENSE

Kilovac

KCS01X024EACA
TE Internal Number: 1618408-3

EU RoHS Compliant
EU ELV Compliant

Contact Arrangement **1 Form X, SPST-NO DM**

Wire Size (AWG) **26**

Contact Current Rating (A) **100**

Coil Voltage (Max) (VDC) **28**

Coil Resistance (Ω) **218**

See All Features

North America

DISTRIBUTOR	QUANTITY	DATE AS OF
MASTER ELECTRONICS CORP. 1-888-473-5297	25	2017/06/06
DIGI-KEY ELECTRONICS 1-800-344-4539	18	2017/06/06
NEWARK ELEMENT14 1-800-463-9275	2	2017/06/05

SAVE TO LIST

FIND SIMILAR PRODUCTS

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Terminal Configuration	**2 x M5 x .8**
	Contactor Type	**Sealed**
	Product Category	**Electromechanical Relays**
	Model	**KCS Series**
	Product Type	**Contactor**
	Product Classification	**Relays - Contactors**
	Arc Cover	**Without**
Configuration Features	Auxiliary Switch Contact Arrangement	**None**
Electrical Characteristics	Coil Voltage (Max) (VDC)	**28**
	Coil Resistance (Ω)	**218**
	Coil Voltage Rating (VDC)	**18 – 28**
	Contact Switching Voltage (Max) (VDC)	**600**
	Actuating System	**DC**
Contact Features	Contact Arrangement	
	Coil Wire Length	**381 mm [15 in]**
Packaging Features	Packaging Method	**Individual**
Other	Torque (in-lbs)	**30 – 40 in-lbs**

© 2017 TE Connectivity Corporation. All Rights Reserved

Compatible Products

Contact Product Support

Downloaded from Arrow.com.