Data sheet

IE-FCI-PWCB-3A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



RoHS COMPLIANT

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Fuse, Fuse insert
Order No.	1543690000
Type	IE-FCI-PWCB-3A
GTIN (EAN)	4050118348859
Qty.	1 items

Downloaded from Arrow.com.

Data sheet

IE-FCI-PWCB-3A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E479289

Dimensions and weights

Net weight	37 g

Temperatures

Storage temperature		Operating temperature	
Installation temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	8bI
REACH SVHC	No SVHC above 0.1 wt%

General data

Product type	Fuse	Insert type	Fuse insert

General standards

Certificate No. (DNV)	TAA000022B	Certificate No. (UR)	E479289

Technical data

Type of connection	Flat-blade receptacles 6.5 mm	Nominal current	3 A
Resistance	0,069 Ω typ.	Operating voltage	32 V DC, 250 V AC
Current-carrying capacity	1.5 kVeff		

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Downloaded from Arrow.com.