
STEALTH BLADE

806 - 896 MHz


SB800 SEE TABLE


Series : **ANTENNA**



PART NO. TABLE

P/N	CABLE LGTH	CONNECTOR
SB800FME12	12.0 FT	FME
SB800MPL12		MPL
SB800SMA12		SMA
SB800TNC12		TNC
SB800FME3	3.0 FT	FME
SB800MPL3		MPL
SB800SMA3		SMA
SB800TNC3		TNC
SB800NS	12.0 FT	NONE
SB80012	12.0 FT	NONE
SB8003	3.0 FT	NONE





All dimensions are in inches

Issue : 0710

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Downloaded from Arrow.com.

STEALTH BLADE

806 - 896 MHz

SB800 **SEE TABLE**

Series : **ANTENNA**

ELECTRICAL SPECIFICATIONS

Frequency :	**806-896**	GHz
Nominal Impedance :		Ω
VSWR :	**1.5:1**	Max
Gain (Overall gain) :	**2.14**	dBi ± 1 dB
Bandwidth @ 1.5 :	**67**	%
Bandwidth @ 2.0 :	**90**	%
Polarization :	**LINEAR**	
Power withstanding :	**3**	W
Connector type :	**SEE TABLE**	
Cable type :	**RG174**	
Length :	**SEE TABLE**	INCHES

MECHANICAL SPECIFICATIONS

Type :	**Dipole**	
Color :	**Black**	
Weight :		oz
Overall length :	**5.16 X .72**	Inches

ENVIRONMENTAL SPECIFICATIONS

Flammability Rating :	**UL E85381**
RoHS complaint :	**Yes**

Issue : 0710

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RoHS COMPLIANT

Downloaded from Arrow.com.