

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Cable marker, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 56



Your advantages

- The US-WMT ... UniSheet labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements

Commercial Data

Item number	0828769
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B12
Product Key	BG2219
Catalog Page	Page 213 (C-3-2019)
GTIN	4046356559836
Weight per Piece (including packing)	12 g
Weight per Piece (excluding packing)	11.6 g
Customs tariff number	39204910
Country of origin	DE

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Technical Data

Product properties

Product type	Conductor marking
Marking	
Number of individual labels	56
Number of individual labels per row	14
Marking technology	
Device	5146464 THERMOMARK CARD
Ink ribbon	5146451 THERMOMARK CARD-US-MAG1 0801371 THERMOMARK-RIBBON 110-TC
Printability	Thermal transfer

Dimensions

Width	23 mm
Length	4.3 mm

Material specifications

Color	white
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Cable / line

Cable structure	
External cable diameter	1.5 mm ... 35 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish	
	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance	
Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions	
Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide	
Specification	following DIN 50018:2013-05

Cable marker - US-WMT (23X4)



0828769

<https://www.phoenixcontact.com/us/products/0828769>

Result	Test passed
Climate level	AHT 1,0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 30 °C / 40 ... 70 % relative humidity. Storage in the original packaging is recommended prior to processing.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-11.0	27281106
ECLASS-10.0.1	27400629

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

Cable marker - US-WMT (23X4)



0828769

<https://www.phoenixcontact.com/us/products/0828769>

Accessories

Conductor marker carrier

Conductor marker carrier - PATG 0/23 - 0828046

<https://www.phoenixcontact.com/us/products/0828046>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 23 x 4 mm

Conductor marker carrier

Conductor marker carrier - PATG 1/23 - 1013847

<https://www.phoenixcontact.com/us/products/1013847>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 23 x 4 mm

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Conductor marker carrier

Conductor marker carrier - PATG 2/23 - 1013850

<https://www.phoenixcontact.com/us/products/1013850>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 23 x 4 mm

Conductor marker carrier

Conductor marker carrier - PATG 3/23 - 1013863

<https://www.phoenixcontact.com/us/products/1013863>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 23 x 4 mm

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Conductor marker carrier

Conductor marker carrier - PATG 4/23 - 0808011

<https://www.phoenixcontact.com/us/products/0808011>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 23 x 4 mm

Conductor marker carrier

Conductor marker carrier - PATG 8/23 - 0808053

<https://www.phoenixcontact.com/us/products/0808053>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 30 ... 35 mm, lettering field size: 23 x 4 mm

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Conductor marker carrier

Conductor marker carrier - PATG 5/23 - 0808024

<https://www.phoenixcontact.com/us/products/0808024>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 23 x 4 mm

Conductor marker carrier

Conductor marker carrier - PATG 6/23 - 0808037

<https://www.phoenixcontact.com/us/products/0808037>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 23 x 4 mm

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Conductor marker carrier

Conductor marker carrier - PATG 7/23 - 0808040

<https://www.phoenixcontact.com/us/products/0808040>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 22 ... 30 mm, lettering field size: 23 x 4 mm

Conductor marker carrier

Conductor marker carrier - PATO 2/23 - 1013902

<https://www.phoenixcontact.com/us/products/1013902>



Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2.8 ... 4.4 mm, lettering field size: 4 x 23 mm

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Cable marker carrier

Cable marker carrier - PAB-KTL 23 - 1013957

<https://www.phoenixcontact.com/us/products/1013957>

Cable marker carrier, transparent, unlabeled, horizontal, mounting type: Assembly with cable ties, cable diameter: > 10 mm, lettering field size: 23 x 4 mm



Magazine

Magazine - TMP-US-MAG1 - 0803341

<https://www.phoenixcontact.com/us/products/0803341>

Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards



Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110/50-TC - 0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374

<https://www.phoenixcontact.com/us/products/0803374>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., width: 110 mm, color: black



Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>

Replacement UV fluid, 23 ml, color: black



Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

Cable marker - US-WMT (23X4)

0828769

<https://www.phoenixcontact.com/us/products/0828769>



Magazine

Magazine - BM ID-ADAPTER PLATE-US - 1044355

<https://www.phoenixcontact.com/us/products/1044355>

Adapter plate for accommodating US sheets



Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com