Part Number : 192150049
Product Description : VersaKrimp Parallel Splice for 3/0 AWG Wire, Carton
Series Number : 19215
Status : Active
Product Category : Splices
Engineering Part Number : K-394



Documents and Resources

Drawings

192150049_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19215
Description	VersaKrimp Parallel Splice for 3/0 AWG Wire, Carton
Product Name	VersaKrimp
Type	Parallel Splice
UPC	800755062694

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	19.142/g
Packaging Type	Carton
Wire Size (AWG)	3/0

Application Tooling

Global

Description	Part Number
Die Set (Large) for the HHLS Hydraulic Crimper	192900028
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	192940008

Downloaded from Arrow.com.

Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

Downloaded from Arrow.com.