Littelfuse® | Carling Technologies®
A Littelfuse® Brand


LRA-Series

Single Pole Lighted Rocker & Paddle Switches

PRODUCT WEBPAGE

request sample, configure part





Since its introduction, the Curvette switch has become the barometer for versatility and performance in the miniature switch market. This lighted version features the very same self cleaning contacts, international approvals, along with a wide variety of circuits, ratings, and actuator options that make the Curvette the switch of choice for various applications.

1	10-16	125-250	6-30
Pole	Amps	VAC	VDC

Typical Applications

- HVAC
- Lighting
- Transportation
- Commercial Food
- Lawn & Garden
- Power Strip

www.carlingtech.com 860.793.9281 sales@carlingtech.com

Downloaded from Arrow.com.

Tech Specs

Dielectric Strength

UL/CSA: 1000V-live to dead metal parts
VDE: 4000V - live to dead metal parts;
750V - across open contacts

Electrical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)

Ordering Scheme

Sample Part Number	LRA911	-	R	S	-	B	/	250N
Selection	1		2	3		4		5

1. SERIES

125 neon lamp (use 125N in Selection 5 Lamp Voltage)
10A 250VAC; 16A 125VAC; 10(4)A 125VACu

	Solder Lugs	.250 Tabs	Wire Leads
OFF-NONE-ON	**LRA210**	**LRA211**	**LRA215**

250 neon lamp (select 250N in selection 5 Lamp Voltage)
15A 250 VAC; 10A 250VAC; 16A 125VAC; 10(4)A 250 T85

	Solder Lugs	.250 Tabs	
OFF-NONE-ON	**LRA910**	**LRA911**	**LRA915**

Incandescent lamp (select 006V-024V in selection 5 Lamp Voltage)
10A 30V

	Solder Lugs	.250 Tabs	Wire Leads
OFF-NONE-ON	**LRA510**	**LRA511**	**LRA515**

2. ACTUATOR STYLE

P	Paddle	**C**	Rocker Clear
R	Rocker translucent		

3. ACTUATOR COLOR

translucent		**clear**	
A	Amber	**A**	Amber
C	White	**C**	Clear
P	Yellow	**G** [1]	Green
S	Red	**B** [1]	Blue
W	Pale Red	**R**	Red

4. BEZEL COLOR/STYLE

STANDARD
B Black (matte)
W White (matte)



OVAL
1 Black (gloss)
2 White (gloss)



5. LAMP VOLTAGE


006V	6 volts incandescent
012V	12 volts incandescent
018V	18 volts incandescent
024V	24 volts incandescent
125N [1]	125 volts neon
250N [1]	250 volts neon


Notes: LED illumination, PC terminals, independent lamps, and additional color options are available. Consult factory.
1 Neon lamps not available with blue or green actuators.
2 Consult factory for additional ratings.


Configure Complete Part Number >
Browse Standard Parts >


Dimensional Specs

inches [millimeters]









MOUNTING HOLE
Panel Thickness: .025 min. - .187 max.
Specific cutout dimension range dependent on panel thickness and material. Consult factory.

*Manufacturer reserves the right to change product specification without prior notice.
Rev: 011025
Downloaded from Arrow.com.