

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)



M12A04ML-12AFL-SBA05

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: N/A
- Shielded: Metal, Non-shielded
- Jacket Material: PUR
- Certificate: UL1977, UL2238, UL1863


You must login first to view the price

Quantity

-

1

+

 Check Stock

 Add to Cart

 Inquiry




Can't find? [Customize your part](#)


Mating Pair & Accessories

Connector Type


 Search




M Series. Accessor...
CAP-WBDMSMA2
-40°C ~ +105°C



M Series. Accessor...
IA-A04F-A04F-0000-01
-20°C ~ +85°C



M Series. M12. A...
M12A-04BFFA-SR7001
-40°C ~ +105°C




M Series. M12. A...
M12A-04BFFB-SL7001
-40°C ~ +105°C

 Add to Cart

 Inquiry

- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >

Specifications		Download / CAD	
Nominal Current 4A		Connector Type Overmolded	
Shielded Metal, Non-shielded		No. of Contacts 04	
Connector Gender Male		Backshell Straight	
Mating Style Screw Thread		IP Rating IPX8	
Assembly Style N/A			
		<div> More Options</div>	

People Also Bought

