


Technical data sheet

Article number:
118-04800 T30ROS



Product Group	Cable ties for thin-walled bundles
Product Family	OS-Series
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)
Application Range	High Temperature and Outdoor Use
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Diameter max (metric)	35.0 mm
Bundle Ø min.	1.6 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	145.0 mm
Min.Tensile Strength	135 N
Operating Temperature	-40 °C to +105 °C
Releasable Closure (Yes/No)	No
Thickness (T)	1.2 mm
Toothing (Serration)	Outside Serrated
Variant	Outside Serrated
Weight/Unit	0.000699 kg
Width (W)	3.4 mm

