

Specification Sheet

Part Number: 133-00997



Separates and secures bundles avoiding abrasion.

Designed to handle both convoluted tubing and bundles not covered in convoluted tubing.

Available in a variety of sizes and colors to be easily identified.

HC Clamp Bundle Separator, Two Hole, PA66HIRGF13, Red, 500/pkg

Article Number 133-00997

Type HC2E

Color Red (RD)

Quantity Per pack

Product Description HC Clamps separate multiple bundles and secure them to brackets or frame rails. Each mount has two pawls for easy pre-installation on a threaded fastener prior to securing with a mechanical fastener. HC Clamps have ribs that make them ideal for convoluted tubing, but they can also be used to separate separate bundles that aren't protected with convoluted tubing.

Short Description HC Clamp Bundle Separator, Two Hole, PA66HIRGF13, Red, 500/pkg

Global Part Name HC2E-PA66HIRGF13-RD

Length L (Imperial)	2.747
Length L (Metric)	67.77
Width W (Imperial)	1.1
Width W (Metric)	27.94
Bundle Diameter Min (Imperial)	0.51
Bundle Diameter Min (Metric)	13.03
Bundle Diameter Max (Imperial)	0.51
Bundle Diameter Max (Metric)	13.03
Bundle Diameter 1st Loop Max (Imperial)	0.513
Bundle Diameter 1st Loop Max (Metric)	13.03
Bundle Diameter 2nd Loop Max (Imperial)	0.513
Bundle Diameter 2nd Loop Max (Metric)	13.03
Height H (Imperial)	1.38
Height H (Metric)	34.94
Mounting Hole Diameter D (Imperial)	0.32 "
Mounting Hole Diameter D (Metric)	8.12 mm

Material	Polyamide 6.6, high impact modified, glass-fiber reinforced (PA66HIRGF13)
Material Shortcut	PA66HIRGF13
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)