

Part Number : [1301350262](#)

Product Description : Super-Safeway Angled GFCI Outlet Box, Feed-Thru, F3 (3/4") Cord Grip Body, Including NEMA 5-20 GFCI & Duplex Receptacles with Flip Lids and 1.83m (6.0') Cord Length, 12/3 SOOW Cord



Series Number : 130135

Status : Active

Product Category : Power Distribution

Engineering Number : 3322FL123

Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130135
Description	Super-Safeway Angled GFCI Outlet Box, Feed-Thru, F3 (3/4") Cord Grip Body, Including NEMA 5-20 GFCI & Duplex Receptacles with Flip Lids and 1.83m (6.0') Cord Length, 12/3 SOOW Cord
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Angled GFCI Outlet Box
UPC	78678828731

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	120V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Cord Type	12/3 SOOW
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	GFCI Duplex

This document was generated on Sep 17, 2025