

Specification Sheet

Part Number: 156-03367

Pre-assembled 2-piece self-affixing tie with coupler

Cable tie head can be moved after bundling

Easy addition of cables after assembly

For parallel routing of bundles that can be twisted 90° even after installation



3-Piece T50R Tie with Coupler, 8" Long, 0.08 - 1.97" Dia, 50lbs, PA66HIRHS, Black, 500/bg

Article Number 156-03367

Type T50RCOUPLER

Color Black (BK)

Quantity Per pack

Product Description The Coupler is the simple way to connect two cable ties for a parallel routing of two bundles. His special design allows the ties 90 degrees of rotation. This is ideal for all applications where the cable, pipe or hose should move flexible in relation to the fixing point. The Coupler can be used with one or two cable ties. This allows easily subsequent installation or replacements of further cables, pipes or hose.

Short Description 3-Piece T50R Tie with Coupler, 8" Long, 0.08 - 1.97" Dia, 50lbs, PA66HIRHS, Black, 500/bg

Global Part Name

T50RCOUPLER-PA66HIRHS/PA66HIR(S)-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.874
Length L (Metric)	202.0
Identification Plate Position	none
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.85
Bundle Diameter Max (Metric)	47.0
Bundle Diameter 1st Loop Max (Imperial)	1.97
Bundle Diameter 1st Loop Max (Metric)	50.0

Bundle Diameter 2nd Loop Max (Imperial) 1.97

Bundle Diameter 2nd Loop Max (Metric) 50.0

Height H (Imperial) 0.33

Height H (Metric) 8.3

Cable Tie Width Max (Imperial) 0.185

Cable Tie Width Max (Metric) 4.70

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Polyamide 6.6, high impact modified, scan black (PA66HIR(S))

Foot Part Material PA66HIR(S)

Material Shortcut PA66HIR(S) PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)