



Search

Products A-Z

Company

News

Careers

Contact

Products

Solutions

Service and Support

Resources

My Phoenix Contact

Home > Products > HMIs and industrial PCs > HMIs and industrial PCs for Ex areas > Product list Panel PCs for Ex areas

> Panel PC - VL2 PPC 7000 EX - 1050365

Panel PC - VL2 PPC 7000 EX - 1050365



ATEX/IECEX compliant and UL listed, IP65-rated Valueline® industrial panel PC (PPC) with a fanless design and Intel® Core™ i5-4300U processor with up to 16 GB of RAM. Mass storage options include HDD and SSD. A single optional PCI or PCIe slot is available.

[Generate product PDF](#)

 This product has to be configured.

PHOENIX CONTACT

586 Fulling Mill Road
Middletown, PA 17057

(800) 888-7388

[Ask a question](#)[Find product experts](#)[Find a distributor](#)[Add to wish list](#)

Configuration

Overview

Technical data

Accessories

Approvals



Your advantages

- ☒ Configurable as a panel PC (PPC)
- ☒ Fanless design for industrial applications
- ☒ ATEX/IECEX Certified
- ☒ Powerful and energy-efficient Intel® Core™ i5 processor
- ☒ Panel PC (PPC): IP65 rating in front panel and IP20 rating in back
- ☒ Easily removable rotating or solid-state hard drives in a variety of sizes



Key Commercial Data

Orderkey	1050365
Packing unit	1 pc
Catalog page	Page 493 (C-6-2019)
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	84715000
Country of origin	TW (Taiwan)

[Create PDF](#)[Send by Email](#)[Feedback](#)[Share](#)