

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [Ceres](#) / [Large Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[Accessory](#)[Large Size](#)[Macro Size](#)[Middle Size](#)[Mini Size](#)[Others \(GBD\)](#)[Others \(MAB\)](#)[Others \(PLD\)](#)[Standard Size](#)[X-Lok](#) >[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 8888](#) >

ABOUT AMPHENOL LTW

[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

DCD-12BFEA-LL7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

[Add to Cart](#)[Inquiry](#)

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



Ceres, Accessory,...
CAP-WADFLCD1
-40°C ~ +105°C



Ceres, Accessory,...
CAP-WADFLMA1
-40°C ~ +105°C



Ceres, Accessory,...
CAP-WADFLMA2
-40°C ~ +105°C



Ceres, Large Size,...
DCD-12AMDM-LL7A01
-20°C ~ +80°C

ABOUT AMPHENOL LTW

[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

[Add to Cart](#)[Inquiry](#)

Specifications

Download / CAD

Nominal Current

20A+5A

Connector Type

Field Installable

Shielded

Plastic, Non-shielded

No. of Contacts

12

Connector Gender

Female

Backshell

Straight

Mating Style

2 Points Lock

IP Rating

IPX7

Assembly Style

Solder

[More Options](#)

People Also Bought

