

	1	2	3	4	5	6	7																																																																
A																																																																							
B	Notes: Material: - Housing Material: Glass filled polyester UL94V-0 - Contact Material: Phosphor Bronze Ø0,45mm Gold flash over Nickel - Shield Material: Copper alloy t=020mm with Nickel plated Electrical: - Voltage Rating: 125VAC RMS - Current Rating: 1.5AMP - Contact Resistance: 30mΩ max. - Insulation Resistance: 500MΩ min. @ 500VDC - Dielectric Withstanding: 1000VAC RMS 50Hz, 1 min. Mechanical: - Durability: 750 cycles min. - PCB Retentionpre-solder: 1 LB min. Environmental: - Storage: -40°C to +85°C - Operation: -20°C to +75°C Package: Tray																																																																						
C																																																																							
D																																																																							
E																																																																							
F																																																																							
G	RoHS compliant Unit: mm <table> <tr> <th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th></th><th></th><th></th></tr> <tr> <td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>.X</td><td>±0.38</td><td></td><td></td><td></td><td></td><td>Drawn</td><td>25.07.2016</td><td>Amy</td></tr> <tr> <td>.XX</td><td>±0.25</td><td></td><td></td><td></td><td></td><td>Approved</td><td>25.07.2016</td><td>Amy</td></tr> <tr> <td>.XXX</td><td>±0.15</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>Angle</td><td>±1.5°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> </table>							Scale	Free								TOLERANCE									.X	±0.38					Drawn	25.07.2016	Amy	.XX	±0.25					Approved	25.07.2016	Amy	.XXX	±0.15								DIM	TOL								Angle	±1.5°								Customer-No.
Scale	Free																																																																						
TOLERANCE																																																																							
.X	±0.38					Drawn	25.07.2016	Amy																																																															
.XX	±0.25					Approved	25.07.2016	Amy																																																															
.XXX	±0.15																																																																						
DIM	TOL																																																																						
Angle	±1.5°																																																																						
H	<table> <tr> <td>①</td><td>Drawn</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td><td></td></tr> </table> components							①	Drawn									Id.	Modification	Date	Name					ASSMANN WSW-No.																																													
①	Drawn																																																																						
	Id.	Modification	Date	Name																																																																			
	1	2	3	4	5	6	7																																																																
								SV4186																																																															