

Pushbutton, 9.1 mm, 1 NO, momentary contact function, 1 NO, bezel yellow



Description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NO

technical data

> general		direct links
Bezel color	yellow	> RAFI eCatalog
Property of bezel / mushroom	opaque	
Collar shape	round	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	80 °C	
illuminated	No	
Soldering time for manual soldering, max.	3 sec	
Soldering temperature for manual soldering	350 °C	
Soldering	Manual soldering	
Packaging	Box	
Packaging unit	10 pcs.	
net weight	1.6 g	
Operating life	40,000 cycles	
B10	52,000 cycles	
Degree of protection, front side, according to DIN EN 60529	IP40	
Minimum order quantity (MOQ)	50 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
> mounting diameters		
Outside dimension, length	11 mm	
Outside dimension, width	11 mm	
Outside dimension, height	30 mm	
Mounting hole	9.1 mm	
Mounting depth	25.5 mm	
Installation height	4.5 mm	
> mechanical data		

Actuation function	momentary contact function
Operating force, max.	7 N
Operating force, min.	7 N
Operating travel, max.	2 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Solder terminal
> electrical data	
Rated voltage, max.	24 V
Rated current, max.	0.1 A