



Part Number : [1211290003](#)

Product Description : mPm DIN Screw M3  
Steel-Zinc Plated, 31.00mm Length, 1 Bag of 100

Series Number : 121129

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 3000-03

---

## Documents & Resources

### Drawings

[Drawing\\_1211290003\\_sd.pdf](#)


### Specifications

[Packaging Specification PK-121129-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2023)8585-DC (23 Jan 2024)  |
| EU RoHS            | Compliant per EU 2015/863   |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | Circular Industrial Connectors                                   |
| Series         | 121129   |
| Description    | mPm DIN Screw M3 Steel-Zinc Plated, 31.00mm Length, 1 Bag of 100 |
| IP Rating      | IP65, IP67   |
| Product Family | mPm DIN Valve Connectors   |
| Product Name   | mPm  |
| Type           | Field Attachable Connector                                       |
| UPC            | 78678846871  |

### Electrical

|                               |     |
|-------------------------------|-----|
| Current - Maximum per Contact | N/A |
| Voltage - Maximum             | N/A |

### Physical

|                               |           |
|-------------------------------|-----------|
| Cable Diameter                | N/A       |
| Coupling Type                 | N/A       |
| Diagnostics / LEDs            | No        |
| Diagnostics Port              | No        |
| Gender                        | N/A       |
| Keyway                        | None      |
| Material - Connector Body     | N/A       |
| Material - Contact            | N/A       |
| Material - Coupling Nut       | N/A       |
| Material - Plating Mating     | n/a       |
| Net Weight                    | 161.500/g |
| Orientation                   | N/A       |
| Pitch - Mating Interface      | N/A       |
| Poles                         | N/A       |
| Temperature Range - Operating | N/A       |
| Wire Size (AWG)               | N/A       |

---

---

This document was generated on Jul 03, 2024