

- 
- Products
- Industry Solutions
- CAREERS
- Resources

- Find Distributor
- Contact Molex



Image not available

Series image - Reference only

Status: Active - Custom

Series: [503772](#)

Category: Molex Parts

Product Environmental Compliance

EU ELV:Not Relevant

EU RoHS:Compliant

EU RoHS Phthalates:Not Contained

China RoHS: 

REACH SVHC:Not Contained Per -ED/01/2017 (12 January 2017)

Low-Halogen Status:Low-Halogen

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products

- Antennas
- Application Tooling
- Cable Assemblies
- Connected Lighting
- Connectors
- Copper Flex
- Electrical Products
- Industrial Automation
- Membrane Switches
- Optical Solutions
- Printed Electronic Solutions

Quick Links

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)
- [Sitemap](#)

Resources

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Mobile Site
- Supplier Portal
- Privacy Policy
- Tradeshow

Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered to their respective owners.

© Copyright 2017

Molex.com would like to place cookies on your computer to help us make this website better.

To find out more about the cookies, see our [Privacy Policy](#). To accept cookies from this site, please click the 'I Accept' button.

I Accept

I Decline