




|                        |                            |
|------------------------|----------------------------|
| Operating force, min.  | 3 N                        |
| Operating travel, max. | 2.7 mm                     |
| Contact function       | 1 NC + 1 NO                |
| Contact system         | Bridge-snap-action contact |
| Contact material       | Silver                     |
| Fixing                 | Threaded ring              |
| Solderability          | Yes                        |
| Terminal on the rear   | Solder terminal            |

> **electrical data**

|                     |        |
|---------------------|--------|
| Rated voltage, min. | 12 V   |
| Rated voltage, max. | 230 V  |
| Rated current, min. | 0.05 A |
| Rated current, max. | 4 A    |

## drawings

### Dimensioned drawing



### Mounting hole drawing

