

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	5-2303237-5 IS ADDED	06SEP2022	PK	SDM
	D	5-2303237-4 IS OBSOLETED	10JAN2024	VR	JN
	D1	PN 5-2303237-4 REACTICATED IN DRAWING	23OCT2024	GV	JN
	D2	5-2303237-5 Obsolete	13JUL2026	AN	JP


2303237-2
AS SHOWN




2303237-3
AS SHOWN




2303237-4
AS SHOWN




2303237-5
AS SHOWN




2303237-6
AS SHOWN




1-2303237-1
AS SHOWN




1-2303237-4
AS SHOWN




D2 5-2303237-5
AS SHOWN




5-2303237-4
AS SHOWN





9-2303237-1
AS SHOWN




2-230327-1
AS SHOWN









2303237-1
AS SHOWN
2:1







TE-PART-NO.	REV.	DESCRIPTION	MATERIAL	DIM A [mm]	DIA D [mm]	FOR CABLE DIAM. [mm]	FOR CABLE CROSS SECTION [mm²]	VOLUME [cm⁻³]	DENSITY [g/cm⁻³]	WEIGHT [g]	COLOUR
D2 5-2303237-5	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	28.9	17.5	16.7...17.3	70	4.49	1.34	6.01	BLACK
5-2303237-4	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	30.2	16.0	15.2...15.8	50	4.57	1.34	6.13	BLACK
9-2303237-1	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	34.9	10.4	9.6...10.2	16	4.95	1.34	6.63	ORANGE SIMILAR RAL 2003
2-2303237-1	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	34.9	10.4	9.6...10.2	16	4.95	1.34	6.63	ORANGE SIMILAR RAL 2003
1-2303237-4	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	30.2	16	15.2...15.8	50	6.12	1.34	8.2	ORANGE SIMILAR RAL 2003
1-2303237-1	B	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	34.9	10.4	9.6...10.2	16	5.87	1.34	7.86	ORANGE SIMILAR RAL 2003
2303237-6	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	25.9	21.1	20.1...20.9	95	4.24	1.34	5.68	ORANGE SIMILAR RAL 2003
2303237-5	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	28.2	18.4	17.4...18.2	70	4.43	1.34	5.94	ORANGE SIMILAR RAL 2003
2303237-4	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	30.2	16.0	15.2...15.8	50	4.57	1.34	6.13	ORANGE SIMILAR RAL 2003
2303237-3	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	32.2	14.6	13.8...14.4	35	4.64	1.34	6.22	ORANGE SIMILAR RAL 2003
2303237-2	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	33.5	12.4	11.6...12.2	25	4.74	1.34	6.35	ORANGE SIMILAR RAL 2003
2303237-1	A	COVER, CABLE SEAL, COMBO DC	PA6 GF10+GB20	34.9	10.4	9.6...10.2	16	4.8	1.34	6.43	ORANGE SIMILAR RAL 2003

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 16742 TG5
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±45°

MATERIAL: SEE TABLE -
FINISH: - -

DWN Aravind H.M 18MAY2016
CHK C.Ringlstetter 18MAY2016
APVD F.Wittrock 18MAY2016
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME COVER, CABLE SEAL, COMBO DC
- -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	-	C-2303237	

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV D2

NOTES

1. TE PART NUMBER SINGLE PART
2. PRODUCTION DATE
3. CAVITY MARKING
4. LETTER INSERT FOR THE PART REVISION
5. UNSPECIFIED GENERAL TOLERANCE TO BE ⌓ 0.6 A B C ALL OVER
6. BULK PACKASING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX
7. TE TRADEMARK ACC. TO SPEC. 1621426-7
8. MATERIAL MARKING ACC. TO VDA 260 UNLESS OTHERWISE STATED

Downloaded from Arrow.com.